

1,2環己烷二羧酸異辛酯 DHEH 1,2-Cyclohexane Dicarboxylic Acid, **Di-2-Ethylhexyl Ester**

說明 Description

DHEH由鄰苯二甲酸二異辛酯氫化而成。是非 鄰苯二甲酸酯可塑劑。DHEH與DHIN兩者之間 的加工特性區別,在許多方面類似如DEHP與 DINP。與DHIN比較,其可塑化效率及延伸率較 佳。適用於食品包裝材、兒童玩具、醫療器材及 吹氣塑膠製品。

DHEH is produced by the hydrogenation of Di(2ethylhexyl)phthalate (DEHP). It is a non-phthalate plasticizer. Although DHEH and DHIN differ in their processing characteristics, DHEH is similar to DEHP and DINP in many ways. When compared to DHIN, its plasticizing efficiency and elongation are better. It is suitable for food wrapping, toys, medical devices, and plastic inflatable products.

CAS No.: 84-71-9 認證 Certificates

專利 Patent	CN 102153469 B, US 8,653,296 B2, TW I414513 B,
FDA	21 CFR 175.105正面表列(Positive List)

規格 Specifications

色		相	Color		APHA	25	Max
酸		價	Acid Value		mg KOH/g	0.05	Max
酯	含	量	Ester Content		Wt %	99.50	Min
加	熱 減	量	Heating Loss	$125^{\circ}C \pm 3^{\circ}Cx3hr$	Wt %	0.10	Max
比		重	Specific Gravity	20/20°C		0.958 ± 0.003	
折	射	率	Refractive Index	25°C		1.460±0.003	
水		份	Water Content		Wt %	0.05	Max
鄰	苯二甲酯	夋 酯	Phthalates Conten	ıt	Wt %	0.015	Max

物性 Physical Properties

分子式 Molecular Formula 構造式 Structural Formula		C ₂₄ H ₄₄ O ₄ O		
			$D-C_{8}H_{17}$	
			$D-C_{8}H_{17}$	
分子量 Molecular Weight		g/mole	396.6	
沸 點 Boiling Point	(~7.5mmHg)	C°	240~250	
閃火點 Flash Point		С	197	
粘 度 Viscosity	(30°C)	cps	27	
流動點 Freezing Point		Ĵ°	27 -50	
包裝 Packing				

Bulk Shipment	Bulk Shipment		
ISO-TANK	ISO-TANK		
液袋或200kg鐵桶	Flexibag or 200kg Metal Drum		
用途 Usage			
● 食品包裝材 ● 兒童玩具 ● PVC可塑糊	Food packaging material		

- 食品包裝材 兒童玩具 PVC可塑糊
- ●醫療器材 ●非鄰苯二甲酸酯塑膠製品...等。

聯絡人 Contact: 賴宏昇 Horng-Sheng Lai

+886 2 2712 2211 EXT.5721 eapublic@npc.com.tw

林訓民 Fred Lin

+886 2 2712 2211 EXT.5723 fredlin@npc.com.tw

南亞塑膠工業股份有限公司 NAN YA PLASTICS CORPORATION 化工第一事業部 · PETROCHEMICAL 1ST. DIV. 台北市敦化北路201號 電話:(02) 2712-2211 EXT 8127 201. TUN HWA N. ROAD, TAIPEI, TAIWAN, R.O.C. TEL : (886-2) 2712-2211 EXT 8127 FAX : (886-2) 2717-8534

• Non-phthalate Plastic Products/ Articles,... etc.

Children Toys
PVC Plastisols

Medical devices